

500 pounds

WARRANTY

YEARS on mattress

YEARS on cover

Leika Atlas Auto Comfort

Without adjustment

TECHNICAL SPECIFICATIONS

Atlas Auto Comfort uses equalization technology to provide maximum redistribution of pressure to prevent injury to the pressure or to support the healing process. In the middle of the mattress, there is a series of ten (10) cylinders in parallel interconnected and closed circuit. The air stays inside cylinders. The dimension varies according to the size of the mattress. They are responsible for distributing the patient's weight. The surface layer is made of high resilience convoluted foam and Serene to maximize patient comfort and support. Flame retardant jersey covering the foams.

Heel section

Presence of a slope with an angle of 5 degrees. She is covered of a new generation of foam: Serene $^{\text{TM}}$. She associates the advantages of memory foam and high resilience foam.

Microclimate cover and handles

The Recovery 5° cover protects the inside of the mattress external contaminants. Presence of handles on the side of the mattress.